


Cover Hinge

Is simply screwed onto the perimeter channel and door edge.


| Cover Hinge | | |
|-------------|----------|----------|
| | Packs of | Part No. |
| Cover hinge | 6 | 1592000 |



Threaded Insert Nuts For KS

Fit in molded fixing nuts on door and inside rear wall of KS enclosures and facilitate mounting of DIN rails, panels, etc.

| Threaded Insert Nuts | | |
|----------------------|----------|----------|
| | Packs of | Part No. |
| Threaded insert nuts | 20 | 1482000 |




Hinges

Can be used to connect covers to housings. A drilling template is included to make installation easy.

Configuration: 1 kit = 2 hinges, 4 installation screws, 4 polyethylene cover caps, 1 drilling template.

| Hinges | | | |
|----------------|------------|----------|----------|
| For enclosures | Material | Packs of | Part No. |
| PK 9517-9523 | polystyrol | 10 kits | 9581000 |




180° Hinges For AE Enclosures

To replace standard 130° hinges (installation hardware included).

Material: die-cast zinc.


| 180° Hinges For AE Enclosures | |
|-------------------------------|----------|
| Packs of | Part No. |
| 2 | 2449000 |



180° Hinges For PS Enclosures

Replace standard 130° hinges, includes installation hardware.


| 180° Hinges For PS Enclosures | | |
|-------------------------------|----------|----------|
| 180° Hinge for | Packs of | Part No. |
| PS | 6 | 4189000 |



130° Hinges For PS Enclosures

For retrofitting a PS door in place of a rear wall.

| 130° Hinges For PS Enclosures | | |
|-------------------------------|----------|----------|
| 130° Hinge for | Packs of | Part No. |
| PS | 6 | 4190000 |



180° Hinges For TS Enclosures

For replacement of TS sheet steel doors with 130° hinges. Door mountings such as the comfort handle may reduce the door opening angle.


Easy assembly:

- Exchange the hinge parts on the frame for 180° hinges (4 screws)
- Drill the door at the pre-marked points
- Attach the hinge parts onto the door
- Align the door into position
- Press the captive hinge pins into place, and it's done!

| 180° Hinges For TS Enclosures | | |
|-------------------------------|----------|----------|
| Packs of | Color | Part No. |
| 4 | RAL 7032 | 8800030 |
| 4 | RAL 7035 | 8800190 |

Configuration: 4 x 180° hinges, including installation hardware; for double doors, two packs are required.

Note: The hinge pins may only be actuated and the door removed with the door open. The hinge cannot be dismantled from the outside with the door closed (access protection).



Hinge For Side Wall For TS Enclosures

The 180° opening angle allows uninhibited access. Assembly may be carried out from either the inside or outside of the enclosure: simply replace 3 enclosure wall fasteners with hinges.


Material: die-cast zinc

Surface finish: textured powder coat RAL 7032.

| Hinge For Side Wall | |
|---------------------|----------|
| Packs of | Part No. |
| 6 | 8800010 |

Configuration: 6 hinges, including installation hardware.

Note: the hinges of the side wall and door must not be fitted on the same enclosure section.




130° Hinges For TS Enclosures

For retrofitting a TS sheet steel door in place of a rear wall.

Material: die-cast zinc

Configuration: 4 x 130° hinges, including installation hardware.

| 130° Hinges For TS Enclosures | |
|-------------------------------|----------|
| Packs of | Part No. |
| 4 | 8800020 |




Fixing Components For Frame For TS Enclosures

For retrofitting a viewing door or sheet steel door in place of a rear wall.

Material: die-cast zinc

Configuration: 4 fixing components including installation hardware.

| Fixing Components For Frame | |
|-----------------------------|----------|
| Packs of | Part No. |
| 4 | 8800040 |



Spring Washer For TS Enclosures


When dismantling the locking rod, the standard spring washers cannot be used again.

Material: spring steel

Surface finish: zinc-plated chromated.

| Spring Washer | |
|---------------|----------|
| Packs of | Part No. |
| 100 | 8800070 |


Note: For a TS8 spring washer installation tool, order Part No. 8800270.



Door Stop

Keeps door open.

| Door Stop | | |
|---------------|----------|----------|
| Door stop for | Packs of | Part No. |
| TS/PS | 5 | 4583000 |
| AE | 5 | 2519000 |



Writing Board

For TS/PS enclosures. Folds up for easy storage. Can be screwed to vertical door rails. These 8" wide units can be joined together to provide a larger writing area.

- 1 unit for 16"/400 mm wide cabinets
- 2 units for 24"/600 mm wide cabinets
- 3 units for 32" and 40"/800 mm wide enclosures.

| Writing Board | | |
|---------------|----------|----------|
| | Packs of | Part No. |
| Writing board | 1 | 4120000 |

